



Yellow-Jacket Copper Grounding Cable, #2

By Chance Lineman Tools & Equipment
Catalog # S6116



Copper Grounding Cable is extra-flexible for handling ease yet strong and tough for long wear. Jacketing is smooth, abrasion, weather and oilresistant in accordance with applicable ASTM Specifications, marked with AWG size approximately every 4 feet. Jackets are T-prene rubber compound with -20°F recommended low temperature. Extra-flexible cables, because of their extra-fine strands, require termination ferrules when used with grounds.

Features

- #2 yellow-jacket copper grounding cable
- To specify cable length, please add a "P" and the length of cable in feet needed to the end of the catalog number.

General

UPC 096359471073

Dimensions

Weight 0.353 lb

Electrical Ratings

Current Rating 200 A
Fault Current - 15 Cycles 14000 A
Fault Current - 30 Cycles 10000 A

Conductor Related

Conductor Size #2 AWG
Diameter - Cable Outside 0.55 In
Diameter - Conductor .32 in
Nema Color Yellow
Strands 665

Product Assets

[Technical Solutions - CH-S6116-SPEC-EN](#)
[Video - CHANCE Temporary Protective Grounding \(VI09071E0620\)](#)
[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-S6116-SPEC-EN | REV 1/2024