



Yellow-Jacket Copper Grounding Cable, 1/0

By Chance Lineman Tools & Equipment
Catalog # [S6117](#)

Copper Grounding Cable is extra-flexible for handling ease yet strong and tough for long wear. Jacketing is smooth, abrasion, weather and oilresistant in accordance with applicable ASTM Specifications, marked with AWG size approximately every 4 feet. Jackets are T-prene rubber compound with -20°F recommended low temperature. Extra-flexible cables, because of their extra-fine strands, require termination ferrules when used with grounds.

Features

- 1/0 yellow-jacket copper grounding cable
- To specify cable length, please add a "P" and the length of cable in feet needed to the end of the catalog number.

General

Catalog Number S6117

Dimensions

Diameter 0.66 in
Weight 0.49 lb

Electrical Ratings



Current Rating 250 A
Fault Current - 15 Cycles 21000 A
Fault Current - 30 Cycles 15000 A

Conductor Related

Conductor Size 1/0 AWG
Diameter - Cable Outside 0.66 In
Diameter - Conductor .41 in
Nema Color Yellow
Strands 1,045

Product Assets

- [Specifications - S6117](#)
- [Video - CHANCE Temporary Protective Grounding](#)
- [Video - CHANCE Temporary Protective Grounding](#)