

Yellow-Jacket Copper Grounding Cable, 4/0

By Chance Lineman Tools & Equipment
Catalog # S6119



Copper Grounding Cable is extra-flexible for handling ease yet strong and tough for long wear. Jacketing is smooth, abrasion, weather and oilresistant in accordance with applicable ASTM Specifications, marked with AWG size approximately every 4 feet. Jackets are T-prene rubber compound with -20°F recommended low temperature. Extra-flexible cables, because of their extra-fine strands, require termination ferrules when used with grounds.

Features

- 4/0 yellow-jacket copper grounding cable
- To specify cable length, please add a "P" and the length of cable in feet needed to the end of the catalog number.

Dimensions

Diameter	0.87 in
Weight	0.745 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A

Conductor Related

Conductor Size	4/0 AWG
Diameter - Cable Outside	0.87 In
Diameter - Conductor	.59 in
Nema Color	Yellow
Strands	2,109

Product Assets

[Video - CHANCE Temporary Protective Grounding](#)

[Video - CHANCE Temporary Protective Grounding](#)