

Clear-Jacket Copper Grounding Cable, 2/0

By Chance Lineman Tools & Equipment
Catalog # S6450



*Representative Image

Copper Grounding Cable is extra-flexible for handling ease yet strong and tough for long wear. Jacketing is smooth, abrasion, weather and oilresistant in accordance with applicable ASTM Specifications, marked with AWG size approximately every 4 feet. Clear jackets (which allow visual inspection of strand conditions) are ultraviolet inhibited Poly Vinyl Chloride (PVC). Recommended low temperature for PVC-jacketed cable is 0°F. Extra-flexible cables, because of their extra-fine strands, require termination ferrules when used with grounds.

Features

- 2/0 clear-jacket copper grounding cable
- To specify cable length, please add a "P" and the length of cable in feet needed to the end of the catalog number.

General

UPC 096359471059

Dimensions

Diameter 0.7 in
Weight 0.539 lb

Electrical Ratings

Current Rating 300 A
Fault Current - 15 Cycles 27000 A
Fault Current - 30 Cycles 20000 A

Conductor Related

Conductor Size 2/0 AWG
Diameter - Cable Outside 0.73 In
Diameter - Conductor .47 in
Nema Color Clear
Strands 1,330

Product Assets

[Video - CHANCE Temporary Protective Grounding](#)
[Video - CHANCE Temporary Protective Grounding](#)