



Standard Platform, 12 ft with Epoxiglas Railing & Fixed Pole Mount

By Chance Lineman Tools & Equipment
Catalog # [T4020619](#)

Designed to provide a convenient workstation on an aerial structure. Bare section near mounting end helps reduce moisture accumulation in inclement weather and provides area between working surface and mount fittings that can be cleaned of dirt and moisture when necessary.

Features

- Furnished Fixed Pole Mount includes chain binder and adjusting wheel
- IMPORTANT: Rail is not suited for use as a fall restraint device
- 500 lbs. Maximum Load Rating
- Three strips of 2 in (51 mm) non-skid tape extend the length of platform surface

General

Catalog Number	T4020619
EU RoHS Indicator	No
Strength Rating - Ultimate	500 lb
Style	Standard Aerial Platform w/ Railing
UPC	096359059073

Dimensions

Dimensions	149 in x 15 in x 11.5 in
------------	--------------------------

Dimensions Metric	378.5 mm x 38.1 mm x 29.2 mm
Height	11.5 in
Height Metric	29.2 mm
Length	149 in
Length Metric	378.5 mm
Weight	140 lb
WeightMetric	63.5 kg
Width	15 in
WidthMetric	38.1 mm

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Installation Manuals - CHANCE® Tools Manuals](#)
- [Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)
- [Specifications - T4020619](#)
- [Video - CHANCE Installation and Safety guide for Platforms](#)