



# Standard Platform, 10 ft with Epoxiglas Railing & Fixed Pole Mount

By Chance Lineman Tools & Equipment  
Catalog # [T4020632](#)

Designed to provide a convenient workstation on an aerial structure. Bare section near mounting end helps reduce moisture accumulation in inclement weather and provides area between working surface and mount fittings that can be cleaned of dirt and moisture when necessary.

## Features

- Furnished Fixed Pole Mount includes chain binder and adjusting wheel
- IMPORTANT: Rail is not suited for use as a fall restraint device
- 500 lbs. Maximum Load Rating
- Three strips of 2 in (51 mm) non-skid tape extend the length of platform surface

## General

EU RoHS Indicator	No
Strength Rating - Ultimate	500 lb
Style	Standard Aerial Platform w/ Railing
UPC	096359059080

## Dimensions

Dimensions	144 in x 16 in x 13 in
Dimensions Metric	365.8 mm x 40.6 mm x 33.0 mm
Height	13 in
Height Metric	33 mm
Length	144 in
Length Metric	365.8 mm
Weight	124 lb
WeightMetric	56.2 kg
Width	16 in
WidthMetric	40.6 mm

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)  
[Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)  
[Video - CHANCE Installation and Safety guide for Platforms](#)



A Hubbell brand