



Insulated Lever Type Wire Cutter For 4/0 Stranded Copper Or 4/0 ACSR, 8 ft 7 in

By Chance Lineman Tools & Equipment
Catalog # T4030687

LEVER TYPE WIRE CUTTER-8FT 7IN- 4/0 ACSR, All cutters are assembled and mounted on Epoxiglas™ insulated poles. A solid fiberglass-reinforced operating rod insulates the linemen from the cutter head. The lever handle is coated with plastisol. The lever action gives the linemen added mechanical force to make clean cuts up to the maximum sizes.

Features

- Three different cutter heads are available for linemen to use for cutting jumper wires, live conductors and tie wires
- All cutters are assembled and mounted on chance Epoxiglas™ insulated poles
- Solid fiberglass-reinforced operating rod insulates linemen from the cutter head
- Lever handle is coated with plastisol
- Lever action gives linemen added mechanical force to make clean cuts

General

Duty	Medium
EU RoHS Indicator	No
Storage Bag Included?	P640-8 (Bag not included. Must be ordered separately.)
Type	Cutters
UPC	096359059318



*Representative Image

Dimensions

Length	102 in
Weight	13.7 lb
WeightMetric	6.2 kg

Conductor Related

Conductor Size	4/0 Stranded Copper or 4/0 ACSR
----------------	---------------------------------

Product Assets

[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)
[Sales Drawings - H1873-6_lever_type_wire_cutters](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-T4030687-SPEC-EN | REV 1/2024