

Dual Range Analog Phasing Meter Kit 1 & 16kV

By Chance Lineman Tools & Equipment

Catalog # [T4030786](#)

DUAL RANGE Phasing Testers easily determine phase relationships and approximate voltage, line-to-line or line-to-ground

Features

- Kit Includes: (1) Phasing Meter, (2) H17601 Six Foot Handles, (1) P6436 Handle Bag, (1) Tester, (2) Hook Probes, (1) Case, (1) Instruction manual
- For convenience on different systems, toggle can switch calibration between two scales on meter face
- Switching to Lo range improves readability for low-end values on Hi scale by increasing needle deflection for more finite readings
- 22-foot-long insulated flexible cable from voltmeter stores on reel on other pole
- Must be used with 2 Epoxiglas Insulating Universal Hotsticks of appropriate length (included in kit)

General

Catalog Number	T4030786
EU RoHS Indicator	No
Style	Analog Dial
UPC	096359059325



*Representative Image

Dimensions

Weight	27.5 lb
WeightMetric	12.4 kg

Electrical Ratings

Withstand Voltage	1kV & 16kV
-------------------	------------

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Instruments and Meters](#)
- [Installation Manuals - CHANCE Phasing Testers Care and Operation Manual](#)
- [Specifications - T4030786](#)
- [Video - CHANCE Meters and Instruments](#)