

Torque Extension Stick for Hydraulic Power Tools 4 ft (1.2 m) Insulating Length



By Chance Lineman Tools & Equipment
Catalog # [T4033009](#)

Insulated torque extension stick permits Live-line work with hydraulic power tools on bucket trucks. .

Features

- Epoxiglas™ Pole is tested per ASTM F711 AND IEC 60855
- Made using heavy duty 1.25" Diameter Epoxiglas Pole
- Insulation Length is 4'
- 75 ft-lb torque rating
- Square Drive on upper end fits any ½"-drive socket
- 7/16" hexagonal quick-connect fitting on bottom couples with a power tool's drive socket
- Handguard is 6" from ferrule with hex fitting

General

Catalog Number	T4033009
EU RoHS Indicator	No
Storage Bag Included?	P643-4 (Bag not included. Must be ordered separately.)
Style	Torque Extension Stick
Torque Rating	75 ft-lbs
UPC	096359060055

Dimensions

Dimensions	72.5 in x 5.5 in x 5.625 in
Dimensions Metric	1841.5 mm x 14.0 mm x 14.3 mm
Height	5.625 in
Height Metric	14.3 mm
Length	72.5 in
Length Metric	1841.5 mm
Weight	5 lb
WeightMetric	2.2 kg
Width	5.5 in
WidthMetric	14 mm

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	-----------------------------------------------------

Product Assets

[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
[Instruction Manual](#)
[Sales Drawings - SA_403-3009](#)
[Specifications - T4033009](#)