

## Telescoping Disconnect Stick 40 ft (12.1 m) Maximum Length

By Chance Lineman Tools & Equipment

Catalog # [T4033349](#)

The Telescoping Tools offer maximum convenience. The universal end fitting on the insulated top section accepts a wide variety of attachments.

### Features

- Tested per OSHA & ASTM F711
- Allow linemen to perform many routine jobs from ground level
- Universal end fitting on insulated top section accepts a wide variety of attachments
- This allows lineman to disconnect switches and replace cutout tubes
- Also allows lineman to remove pole covers, prune trees, plus other overhead tasks
- Sticks retract to approximately 5 ft. for easy truck transport (even in most cab sections)
- Heavy-duty, spring-loaded plastic buttons keep extended tool sections locked in place
- As each section extends and slightly twists, buttons also pop securely into place

### General

Catalog Number	T4033349
EU RoHS Indicator	No
UPC	096359329152

### Dimensions

Diameter - Rod / Tube	2.5 in
Dimensions	80.125 in x 5.5 in x 5 in



\*Representative Image

Dimensions Metric	203.5 mm x 14.0 mm x 12.7 mm
Height	5 in
Height Metric	12.7 mm
Length	80.125 in
Length - Retracted	6.25 ft
Length - Retracted Metric	1.8 m
Length Metric	203.5 mm
Lengths - Extended	* 22 ft * 28 ft * 34 ft * 40 ft
Weight	12 lb
WeightMetric	5.4 kg
Width	5.5 in
WidthMetric	14 mm

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Insulated Hand Tools](#)  
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)  
[Instruction Manual](#)  
[Sales Drawings - Telescopic Hotstick](#)  
[Specifications - T4033349](#)