

Ground Clamp, C-Type, Type I-Class A-Grade 2, 0.814" Jaw Opening

By Chance Lineman Tools & Equipment

Catalog # [T6000465](#)

Ground Clamp, C-Type, Type I-Class A-Grade 2, 0.814" Jaw Opening



Features

- C-Type Ground Clamp
- Continuous Current 250A
- Fault Current 21kA for 15 cycles or 15kA for 30 cycles
- Main Line Range Max. 477kcmil ACSR (0.814")
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 1/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 2
- Jaws Smooth
- Ferrule Threaded

General

Catalog Number	T6000465
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Bronze
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
Thread Type	Threaded
Torque Rating	200 in-lbs
UPC	096359061021

Dimensions

Jaw Opening Size - Maximum	.814 in
Jaw Opening Size - Minimum	.162 in
Weight	1.284 lb

Electrical Ratings

Current Rating	250 A
Fault Current - 15 Cycles	21000 A
Fault Current - 30 Cycles	15000 A
Grounding Wire Capacity Maximum	1/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Fault Current - ASTM Grade	ASTM Grade 2

Logistics

Pallet Quantity	1440
-----------------	------

Product Assets

[Catalogs - Grounding Equipment Specifications - T6000465](#)