



Temporary Grounding Set Kit - REA - #2 Cables - 3x6ft. - 1x12ft. - 1X30ft. - C6002276 C-Clamps - G3370 Ground Rod - T6001549 Cluster Bar

By Chance Lineman Tools & Equipment
Catalog # [T6000641](#)

Temporary Grounding Set Kit - REA - #2 Cables - 3x6ft. - 1x12ft. - 1X30ft. - C6002276 C-Clamps - G3370 Ground Rod - T6001549 Cluster Bar



Features

- This complete set of grounds, cable and accessories gives all of the equipment needed for many types of distribution structures in one easy-to-use kit
- The ferrules are factory crimped to the grounding cable
- Set includes C6002276 C-clamps for conductors ranging from #8 to 1033 kcmil ACSR
- Cluster bar, T6001549, and ground rod, G3370, are also included

General

Bolt Installation Torque (Recommended)	20 ft-lbs
EU RoHS Indicator	No
UPC	096359061083

Dimensions

Weight	48 lb
--------	-------

Electrical Ratings

Fault Current - 15 Cycles	14000 A
Fault Current - 30 Cycles	10000 A

Logistics

Pallet Quantity	18
-----------------	----

Product Assets

[Catalogs - Grounding Equipment](#)

[Video - CHANCE Temporary Protective Grounding](#)