



Ground Clamp, C-Type, Type I- Class A-Grade 6H, 2.0" Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # T6000658

Ground Clamp, C-Type, Type I-Class A-Grade 6H, 2.0" Jaw
Opening



Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current - ASTM Grade 6H
- Main Line Range Max. 2" O.D. Bus
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 6H, Jaws Smooth
- Drilled ferrule hole for threaded ferrule

General

Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
UPC	096359061090

Dimensions

Jaw Opening Size - Maximum	2 in
Jaw Opening Size - Minimum	.162 in
Weight	2.45 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications And Compliance

Fault Current - ASTM Grade	6H
----------------------------	----

Logistics

Carton Quantity	15
Pallet Quantity	450

Product Assets

[Catalogs - Grounding Equipment](#)
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs](#)
[Sales Drawings - SA_600-0658](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-T6000658-SPEC-EN | REV 6/2024