


Ground Clamp - All Angle I-B-5 2.88" Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # T6001693



*Representative Image

All-Angle.

Features

- All-Angle Grounding Clamps
- Aluminum Bodies with Serrated Jaws
- For installation ease, jaws pivot 75° left or right.
- Tapped for 5/8"-11 UNC threaded ferrule

General

EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
UPC	096359247395

Dimensions

Jaw Opening Size - Maximum	2.88 in
Jaw Opening Size - Minimum	1.66 in
Weight	3.195 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)