



6ft. #2 Chisel-Point Temporary Grounding Set for URD Cable with Ground Rod

By Chance Lineman Tools & Equipment
Catalog # T6002234



*Representative Image

6ft. #2 Chisel-Point Temporary Grounding Set for URD Cable with Ground Rod

Features

- For temporary grounding of underground distribution cable with jacket over concentric neutral
- Used to confirm the cable that will be worked on is de-energized
- Chisel-point ensures contact with center conductor
- Chisel-point clamp main-line capacity is 1-1/2in.
- C-clamp in chisel-point sets fits conductors from #6 (0.162in.) to 2.0in. O.D. bus
- Each set includes 6ft. of #2 copper clear-jacket ground cable and ferrules, a chisel clamp and C-clamp
- Includes 24in. screw-in copper-clad ground rod for easy handling

General

EU RoHS Indicator No
UPC 096359061700

Dimensions

Jaw Opening Size - Maximum 2 in
Jaw Opening Size - Minimum .162 in
Weight 12.74 lb

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)
[Technical Solutions - CH-T6002234-SPEC-EN](#)
[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-T6002234-SPEC-EN | REV 1/2024