

## Ground Set Cluster 2/0 Clear 3 x 6' Ball-Socket Clamps & Ball-Studs

By Chance Lineman Tools & Equipment  
Catalog # [T6002246](#)

Each Ball-Stud set includes a three-way copper terminal block, four bronze ground clamps, four ball-studs, and three 6-ft. lengths of 2/0 copper clear-jacket ground cable with threaded aluminum ferrules. Ball-studs are C600-2102 and the ball-stud clamps are C600-2100.

### Features

- Includes a three-way copper terminal block, Four bronze ground clamps
- Three 6' lengths of 2/0 copper clear-jacket ground cable with threaded-stud ferrules, and 4 ball studs
- Fault current ratings: 27kA for 15 cycles or 20kA for 30 cycles
- ASTM Type I, Class A, Grade 3
- Ball-studs are C600-2102 and the ball-stud clamps are C600-2100

### General

Bolt Installation Torque (Recommended)	20 ft-lbs
EU RoHS Indicator	No
Power Supply	
Shrouded?	
Style	
Swivel Top?	
Thread Size	
Type	
UPC	096359061724

### Dimensions

Jaw Width	
Length	6 ft
Weight	19.6 lb

### Electrical Ratings

Amperage - Display Range	
Amperage Rating	27000 A
Fault Current - 15 Cycles	27000 A
Fault Current - 30 Cycles	20000 A
Withstand Voltage	



### Conductor Related

Strands

### Product Assets

[Catalogs - Grounding Equipment](#)

[Video - CHANCE Temporary Protective Grounding](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CLTE-T6002246-SPEC-EN | REV 6/2024