



Grade 5 Long Grounding Ball Stud 1in. (25mm)

By Chance Lineman Tools & Equipment
Catalog # [T6002364](#)



Grade 5 Long Grounding Ball Stud 1in. (25mm)

Features

- Designed and tested to ASTM F855 Grade 5 withstand rating of 43kA for 15 cycles or 30kA for 30 cycles
- For use with 1in. (25mm) ball stud clamps
- 3in. nominal shank length
- 7in. overall length
- 2-3/4in. threaded shank with 1/2in.-13 UNC
- Tin plated

General

Bolt Installation Torque (Recommended)	25 ft-lbs
Catalog Number	T6002364
UPC	096359061762

Dimensions

Length	7 in
Weight	0.784 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

- [Catalogs - Grounding Equipment](#)
- [Sales Drawings - Long Ball Stud](#)
- [Specifications - T6002364](#)
- [Video - CHANCE Temporary Protective Grounding](#)
- [Video - CHANCE Temporary Protective Grounding](#)



A Hubbell brand