

## Ground Set 3 Phase 1/0 Clear 3 x 4' Phase Leads and 1 x 6' Ground Lead

By Chance Lineman Tools & Equipment  
Catalog # [T6002375](#)



Flat-Face-Clamp set includes a four-way bronze terminal block, one 6-ft. and three 4-ft. lengths of 1/0 copper clear-jacket ground cable with shrouded plain-plug copper ferrules, three aluminum grounds with bronze eye-screws (G3363-3SJ) and one with bronze T-handle (G3363-4SJ).

### Features

- Flat-Face-Clamp set includes a four-way bronze terminal block, one 6-ft. and three 4-ft. lengths of 1/0 copper clear-jacket ground cable with shrouded plain-plug copper ferrules, three aluminum grounds with bronze eye-screws (G3363-3SJ) and one with bronze T-handle (G3363-4SJ)
- Fault current ratings of 21kA for 15 cycles or 15kA for 30 cycles

### General

Bolt Installation Torque (Recommended)	20 ft-lbs
EU RoHS Indicator	No
Power Supply	
Shrouded?	
Style	
Swivel Top?	
Thread Size	
Type	
UPC	096359061779

### Dimensions

Jaw Width	
Weight	19.6 lb

### Electrical Ratings

Amperage - Display Range	
Amperage Rating	21000 A
Fault Current - 15 Cycles	21000 A
Fault Current - 30 Cycles	15000 A
Withstand Voltage	

### Conductor Related

Strands

### Product Assets

[Catalogs - Grounding Equipment](#)

[Video - CHANCE Temporary Protective Grounding](#)



A Hubbell brand