

## Cutout Ground Clamp w/ rated T-Stud Terminal

By Chance Lineman Tools & Equipment

Catalog # [T6002567](#)

Cutout Ground Clamp w/ rated T-Stud Terminal

### Features

- Fault Current rating: 20,000 amps for 30 cycles
- Used to ground bottom hinge contact on cutouts used on distribution riser poles or where grounding is required
- Fits CHANCE F2, F3, and C Cutouts
- Also fits Westinghouse LDX, Southern States B-80, Southern States Series 63, Joslyn S&C Type SX, McGraw-Edison LMO, and GE Durabute cutouts
- Clamp can be installed with or without grounding cable
- Clamp's drilled terminal accepts threaded-stud cable ferrules
- Also accepts threaded L-Stud and T-Stud Terminals (3/4" diameter bronze) for use with conventional ground clamp cable sets
- Does not include cutout

### General



Catalog Number	T6002567
EU RoHS Indicator	No
Eye Screw/T-Handle	N/A
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
UPC	096359346036

### Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

### Product Assets

[Catalogs - Grounding Equipment](#)  
[Specifications - T6002567](#)