

1in. (25mm) Grade 5 Grounding Ball Stud with Internal Threads

By Chance Lineman Tools & Equipment
Catalog # [T6002867](#)



1in. (25mm) Grade 5 Grounding Ball Stud with Internal Threads

Features

- Designed and tested to ASTM F855 Grade 5 withstand rating of 43kA for 15 cycles or 30kA for 30 cycles
- For use with 1in. (25mm) ball stud clamps
- 3.3in. overall length
- 1in. Internal threads 1/2in.-13 UNC
- Tin plated

General

Bolt Installation Torque (Recommended)	300 in-lbs
Catalog Number	T6002867
UPC	096359371960

Dimensions

Dimensions	3.3 in x 1.16 in x 1.16 in
Height	1.16 in

Length	3.3 in
Weight	0.5 lb
Width	1.16 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Fault Current - ASTM Grade	5
Industry Standard(s)	ASTM

Product Assets

- [Catalogs - Grounding Equipment](#)
- [Sales Drawings - SA T6002867 1 INCH - 25MM BALL STUD - FEMALE THREAD](#)
- [Specifications - T6002867](#)
- [Video - CHANCE Temporary Protective Grounding](#)
- [Video - CHANCE Temporary Protective Grounding](#)