



Ground Clamp, Flat-Face, Drilled T-Handle, ASTM Grade 5

By Chance Lineman Tools & Equipment
Catalog # [T6003009](#)

Ground Clamp, Flat Face, Fine-Threaded T-Handle, drilled for threaded ferrule, ASTM Grade 5

Features

- Flat Face Ground Clamp
- Continuous Current 400A
- Grade 5 Fault Current Rating 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 1.5" Angles and 1.5" Flats
- Main Line Range Min. 1/8"
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type III, Class B, Grade
- Jaws Serrated
- Ferrule Threaded

General

Catalog Number	T6003009
EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb (set screws finger tight)
Installation Torque (in-lb)	tight)
Ferrule Installation Torque (in-lb)	250 in-lb



UPC 096359372028

Dimensions

Dimensions	8.7 in x 5 in x 2.75 in
Height	2.75 in
Jaw Opening Size - Maximum	1.5 in
Jaw Opening Size - Minimum	0.125 in
Length	8.7 in
Weight	2 lb
Width	5 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Fault Current - ASTM Grade	5
Industry Standard(s)	ASTM

Product Assets

[Catalogs - Grounding Equipment](#)
[Specifications - T6003009](#)



A Hubbell brand