

Ground Clamp, C-Type, 6H

By Chance Lineman Tools & Equipment
Catalog # T6003011

6H C-Type Ground Clamp with eye screw, smooth jaw, ASTM Grade 6H, threaded ferrule hole, 2" jaw opening



Features

- Grade 6H Rated
- Rated 55kA with X/R = 30
- First cycle current peak = 148kA
- Last cycle current peak = 82kA
- Test duration = 15 cycles

General

Catalog Number	T6003011
EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
UPC	096359372035

Dimensions

Weight 1.75 lb

Certifications And Compliance

Fault Current - ASTM Grade 6H

Logistics

Pallet Quantity 720

Product Assets

[Catalogs - Grounding Equipment](#)
[Literature - New Chance® 6H Grounding C-Clamp](#)
[Sales Drawings - SA_600-0658](#)
[Specifications - T6003011](#)