

Tongue Type Strain Jack for Strain Poles, 24 in (0.6 m)

By Chance Lineman Tools & Equipment
Catalog # [V4010157](#)



ASSEMBLY, 24" SCREW JACK, Acme Thread Strain Jack.

Features

Strain Jack (24" Long) Tongue Type

General

EU RoHS Indicator	No
Style	Accessories
UPC	096359205173

Dimensions

Dimensions	31.25 in x 2.5 in x 1 in
Dimensions Metric	79.4 mm x 6.4 mm x 2.5 mm
Height	1 in
Height Metric	2.5 mm
Length	31.25 in
Length Metric	79.4 mm
Weight	4.4 lb
WeightMetric	2 kg
Width	2.5 in
WidthMetric	6.4 mm

Product Assets

[Literature - Transmission Project Tools and Equipment Checklist](#)