

# Tap Box

By Connector Mfg. Co. (CMC)  
Catalog # [LWTE10-750GSS](#)

A Completely customizable solution to meet your specific application needs!

## Features

- Key Options available but not limited to: Common configurations available for tight deadlines
- Available with CMC's unique lay-in feature mechanical bars, (Each lay-in connection has a removable "keeper" that allows conductors to be laid into the outlet, solving the problem of trying to bend large conductors in confined areas)
- Connectors included are fabricated from 6061-T6 aluminum alloy for conductivity and strength, fully tested to ANSI C119.4 for Class "A" connectors
- Cabinets available in aluminum, mild steel, and stainless steel
- Cabinets are available with oven cured powder coat polyester or can be ordered bare
- Available wall or pad mounted, all mounting hardware is 18-8 stainless steel
- Offered with removable swinging doors with stainless steel lift off hinges
- Separate pad lockable hasp for added security
- Available in single and double door configurations
- Available in single or three-phase options up to 6000A depending upon the required configuration
- Range taking mechanical connections
- Utilized for both overhead and underground services



- Knockout locations available for both top and bottom feeds

## General

Catalog Number	LWTE10-750GSS
Material	12 GA 316 SS
UPC	192663182480

## Dimensions

Depth	14 in
Height	38 in
Width	20.75 in

## Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• NEMA 3R Compliant</li><li>• ANSI C57</li></ul>
------------------	--

## Product Assets

[360 Product View - CMC\\_LWTE10-750GSS](#)  
[3D Product View - CMC\\_LWTE10-750GSS](#)  
[Literature - Tap Box Enclosures](#)  
[Sales Drawings - UB22701349-S](#)  
[Specifications - LWTE10750GSS](#)