



## 4.5" Round Shaft Lead (RS4500.237), 10/12/14 x 10ft

By CHANCE Foundation Solutions  
Catalog # [C1071504](#)

RS4500.237, 120" long with 10", 12", 14" helices.



\*Representative Image

### Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

### Application

Helical Anchoring

### General

Capacity - Plate Grade	80
Coating	Galvanized
Finish Type	Galvanized
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	6
Number of Helices	3
Shaft Type	RS
Torque Rating	19000 ft-lbs
Type	Lead Sections
UPC	096359652304

### Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in
Length	120.00 in
Length - Effective	118.50 in
Weight	154.00 lb

### Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E\\_0419\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)
- [Video - Hubbell Power Systems Helical Pile Shake Table Testing \(VIO4112E\)](#)
- [Video - CHANCE® Square Shaft Installation \(VIO4148E0819\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C1071504-SPEC-EN | REV 1/2024