



1.5" Square Shaft Helical Extension (SS 150), 14/14/14 x 10ft

By CHANCE Foundation Solutions
Catalog # [C1100475](#)

SS150, 123" long with 14",14",14" helices.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	7000 ft-lbs
Type	Anchor Extensions
UPC	096359009825

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Length	120.00 in
Weight	138.837 lb

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)

Related Products

- [C1500146](#)
- [C1500145](#)
- [C1500175](#)
- [C1500144](#)
- [639001](#)



A proud member of the Hubbell Family.