



1.75" Square Shaft Helical Extension (SS175), 14/14/14 x 10ft

By CHANCE Foundation Solutions
Catalog # [C1100476](#)

SS175, 123" long with 14",14",14" helices.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb.
Torque Rating	10500 ft-lbs
Type	Anchor Extensions
UPC	096359009832

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Length	120.00 in
Weight	167.580 lb

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [Sales Drawings - SS175 Anchors \(SA11010018\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)



A proud member of the Hubbell Family.