



## 2" Square Shaft Extension (SS200), 10ft

By CHANCE Foundation Solutions  
Catalog # [C1100566](#)

SS200, 10' (3048 mm) ft long with no helix



### Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

### Application

Helical Anchoring

### General

Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Anchor Extensions
UPC	096359243298

### Dimensions

Dimensions	120.00 in x 3.250 in x 5.000 in
Height	5.000 in
Length	120.00 in
Weight	147.412 lb
Width	3.250 in

### Logistics

Pallet Quantity	12
Standard Package	1

### Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Catalogs - CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E\\_0419\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [Sales Drawings - SS200 Anchors \(SA11010019\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

### Related Products

- [P0010030P](#)
- [P0011445P](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C1100566-SPEC-EN | REV 1/2024