



## 1.5" Square Shaft Helical Extension (SS5), 8/8/8 x 7ft (NG)

By CHANCE Foundation Solutions  
Catalog # [C1100689NG](#)

SS5, 84" long with 8", 8", 8" helices (NG).



### Features

- Finish: Ungalvanized
- Capacity of helical pile can be determined by measuring installation

### Application

Helical Anchoring

### General

Capacity - Plate Grade	50
Coating	Ungalvanized
Finish Type	Ungalvanized
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	10
Number of Helices	3
Shaft Type	SS
Torque Rating	5700 ft-lbs
Type	Anchor Extensions
UPC	096359765998

### Dimensions

Anchor Helix Diameter(s)	8 in - 8 in - 8 in
Length	84.00 in
Length - Effective	80.19 in
Weight	69.80 lb

### Logistics

Pallet Quantity 12

### Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)  
[Literature - New Construction Helical Pile Foundation System \(SF04215E\\_0419\)](#)  
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)

### Related Products

[P0010041P](#)  
[055449P](#)  
[639001](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C1100689NG-SPEC-EN | REV 1/2024