



1.5" Square Shaft Helical Extension (SS5), 8/8 x 5ft

By CHANCE Foundation Solutions
Catalog # [C1100690](#)



SS5, 60" long with 8", 8" helices.

Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Capacity - Plate Grade	50
Coating	Galvanized
Finish Type	Galvanized
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	10
Number of Helices	2
Shaft Type	SS
Torque Rating	5700 ft-lbs
Type	Anchor Extensions
UPC	096359239703

Dimensions

Anchor Helix Diameter(s)	8 in - 8 in
Dimensions	60.00 in x 8.00 in x 8.00 in
Height	8.00 in
Length	60.00 in
Length - Effective	57.19 in
Weight	51.30 lb
Width	8.00 in

Logistics

Pallet Quantity 12

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Engineering Drawing - Soil Screw Retention Wall System](#)
[Engineering Drawing - Soil Screw Retention Wall System](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[SDS - MSDS - Galvanized Steel Products](#)

Related Products

[639001](#)
[P0010041P](#)
[055449P](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C1100690-SPEC-EN | REV 1/2024