



SS5, 60" long with 8",8" helices Soil Screw®

By CHANCE Foundation Solutions
Catalog # [C1100692](#)

SS5, 60" long with 8",8" helices.



Features

- Finish: Ungalvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Capacity - Plate Grade	50
Coating	Ungalvanized
EU RoHS Indicator	No
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	10
Number of Helices	2
Shaft Type	SS
Torque Rating	5700 ft-lbs
Type	Lead Sections
UPC	096359239666

Dimensions

Anchor Helix Diameter(s)	8 in - 8 in
Length	60.00 in
Length - Effective	52.91 in
Weight	49.40 lb

Logistics

Pallet Quantity 12

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Engineering Drawing - Soil Screw Retention Wall System](#)
[Engineering Drawing - Soil Screw Retention Wall System](#)
[Engineering Drawing - Soil Screw Retention Wall System](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Soil Screw® Wall Anchors - Retention Wall System \(BR04154E\)](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - HUBBELL®L CHANCE® Helical Tieback \(VI104175E\)](#)

Related Products

[639001](#)
[C1100690](#)
[C1100689](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C1100692-SPEC-EN | REV 1/2024