



Pole Base Foundation, 8-5/8" OD x 60" Long

By CHANCE Foundation Solutions
Catalog # [C11242NG4TJ](#)

Streetlight Foundation (SLF) 8.625 OD x 60" Long, 1" thick x 12" square baseplate, fixed circle, hardware included.



*Representative Image

Features

- Fixed 10-1/2" Bolt Circle
- 4 holes, 1" Dia x 2-1/2" Long
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

Application

Helical Anchoring

General

Base Plate Shape	Square
Bolt Hole Type	Tapped Bolt Hole
Coating	Galvanized
Ground Lug Hole	No
Number of Bolt Holes	4
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359010234

Dimensions

Base Plate Dimensions	12.00 in
Base Plate Thickness	1.000 in
Bolt Length	2.50 in
Cableway Distance From Base	12 in
Cableway Length	12.00 in
Cableway Width	2.50 in
Center hole dimensions	5.00 in
Diameter - Bolt	1 in
Diameter - Bolt Circle	10.5 in
Foundation Diameter	8.630 in
Foundation Length	60 in
Length	60.00 in
Weight	166.000 lb

Logistics

Pallet Quantity	9
Standard Package	1

Product Assets

[Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
[Engineering Drawing - SA11242NG4TJ](#)
[Installation Manuals - Instant Foundations \(TD04365E\)](#)
[Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
[Literature - Precast Concrete Collars \(SF04273E\)](#)
[Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
[Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
[Sales Drawings - SA11242NG4TJ](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
[Video - CHANCE Instant Foundation & Concrete Collar \(VI04163E0520\)](#)
[Video - SLF \(VI04173E1021\)](#)
[Video - CHANCE® Streetlight Foundation \(VI04147E0719\)](#)

Related Products

[C3030139](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C11242NG4TJ-SPEC-EN | REV 1/2024

