



1.5" Square Shaft Lead (SS5), 10 x 7ft

By CHANCE Foundation Solutions
Catalog # [C1500003](#)

SS5, 84" long with 10" helix.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Capacity - Plate Grade	50
Coating	Galvanized
Finish Type	Galvanized
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	10
Number of Helices	1
Shaft Type	SS
Torque Rating	5700 ft-lbs
Type	Lead Sections
UPC	096359011477

Dimensions

Anchor Helix Diameter(s)	10 in
Length	84.00 in
Length - Effective	76.16 in
Weight	61.80 lb

Certifications and Compliance

ICC-ES Evaluated	ESR 2794
LARR Certified?	RR 25984

Logistics

Pallet Quantity 20

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Engineering Drawing - SS5 Screw Anchors 1-1/2" SS](#)
[Literature - CHANCE® Building Code Evaluated Products December 2022](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Sales Drawings - SS5 Screw Anchors 1-1/2" SS](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Test Documents - ICC Evaluation \(NER2794\)](#)
[Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)

Related Products

[C1500047](#)
[C1500896](#)
[C1500009](#)
[C1500008](#)
[C1500048](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C1500003-SPEC-EN | REV 1/2024