



# 1.75" Square Shaft Extension(SS175), 7ft

By CHANCE Foundation Solutions  
Catalog # [C1500014](#)

SS175, 84" long no helix.



### Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

### Application

Helical Anchoring

### General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	10
Shaft Type	SS
Torque Rating	10500 ft-lbs
Type	Anchor Extensions
UPC	096359011583

### Dimensions

Length	83.50 in
Length - Effective	78.80 in
Weight	76.10 lb

### Certifications and Compliance

CCMC Compliant?	CCMC 13193-R
ICC-ES Evaluated	ESR 2794
LARR Certified?	RR 25984

### Logistics

Pallet Quantity 24

### Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - CHANCE Helical Solutions Product Catalog (CA04140E)
- Engineering Drawing - SS175 Extensions
- ISO Certificates - Centralia\_Operations\_ISO\_9001\_2015
- Literature - New Construction Helical Pile Foundation System (SF04215E\_0419)
- Literature - CHANCE® Building Code Evaluated Products December 2022
- Literature - Square Shaft Efficient Helical Pile Design (BR04326E)
- Sales Drawings - SS175 Extensions
- SDS - MSDS - Galvanized Steel Products
- Test Documents - ICC Evaluation (NER2794)

### Related Products

- [055591P](#)
- [P0011443P](#)
- [C3030195](#)



A proud member of the Hubbell Family.