



## 3.5" Round Shaft Extension(RS3500.300), 5ft

By CHANCE Foundation Solutions  
Catalog # [C1500025CU](#)

RS3500.300, 60" long with no helix.



### Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

### Application

Helical Anchoring

### General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	7
Shaft Type	RS
Torque Rating	13000 ft-lbs
Type	Anchor Extensions
UPC	096359709916

### Dimensions

Length	62.00 in
Length - Effective	56.00 in
Weight	60.00 lb

### Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - CHANCE Helical Solutions Product Catalog (CA04140E)
- Engineering Drawing - SA1070573CU
- ISO Certificates - Centralia\_Operations\_ISO\_9001\_2015
- Literature - New Construction Helical Pile Foundation System (SF04215E\_0419)
- Sales Drawings - SA1070573CU
- SDS - MSDS - Galvanized Steel Products
- Video - CHANCE 4.3 Helicap 3.0 Torque Graph (VIO4167E0420)
- Video - CHANCE 4.2 Helicap 3.0 Capacity Graph Tab (VIO4165E0420)
- Video - Hubbell Power Systems Helical Pile Shake Table Testing (VIO4112E)

### Related Products

- [450315P](#)
- [P1100814P](#)
- [058331P - Single-Coil Spring Lockwasher for 3/4-in bolt](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CN-C1500025CU-SPEC-EN | REV 7/2023