



Standard Underpinning Bracket

By CHANCE Foundation Solutions
Catalog # [C1500299](#)

Standard Underpinning Bracket (Std) fits SS175.



Features

- Finish: Galvanized
- Building Code Approved: Yes
- Bracket Only (includes hardware)

Application

Helical Anchoring

General

Coating	Hot Dip Galvanized
Shaft Type	SS
Strength Rating - Ultimate	40000 lb
Type	Underpinning
UPC	096359241430

Dimensions

Weight	36.30 lb
--------	----------

Certifications and Compliance

ICC-ES Evaluated	ESR 2794
LARR Certified?	RR 25984

Logistics

Pallet Quantity	50
-----------------	----

Product Assets

[Catalogs - CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)

[Engineering Drawing - Standard Underpinning Bracket - 80 KIP](#)

[Installation Manuals - Underpinning Brackets C150-0121 and C150-0299 Installation Instructions](#)

[ISO Certificates - Centralia_Operations_ISO_9001_2015 Literature - CHANCE® Building Code Evaluated Products December 2022](#)

[Sales Drawings - Standard Underpinning Bracket - 80 KIP](#)

[SDS - MSDS - Galvanized Steel Products](#)

[Test Documents - ICC Evaluation \(NER2794\)](#)

[Video - CHANCE 4.3 Helicap 3.0 Torque Graph \(VIO4167E0420\)](#)

[Video - CHANCE 4.2 Helicap 3.0 Capacity Graph Tab \(VIO4165E0420\)](#)

[Video - Hubbell Power Systems Helical Pile Shake Table Testing \(VIO4112E\)](#)

Related Products

[C1500488](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CN-C1500299-SPEC-EN | REV 7/2023