



## 2" Square Shaft Lead (SS200), 8/10/12 x 7ft

By CHANCE Foundation Solutions  
Catalog # [C1500403](#)

SS200, 84" long with 8",10",12" helices.



### Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

### Application

Helical Anchoring

### General

Capacity - Plate Grade	80
Coating	Hot Dip Galvanized
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	10
Number of Helices	3
Shaft Type	SS
Torque Rating	16000 ft-lbs
Type	Lead Sections
UPC	096359294115

### Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in
Length	86.25 in
Length - Effective	78.94 in
Weight	134.60 lb

### Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)  
[Catalogs - CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)  
[Engineering Drawing - Helical PULLDOWN® Micropile Installation Manuals - IS-200FTI\\_Rev\\_A\\_Oct\\_2016](#)  
[ISO Certificates - Centralia\\_Operations\\_ISO\\_9001\\_2015](#)  
[Literature - New Construction Helical Pile Foundation System \(SF04215E\\_0419\)](#)  
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)  
[SDS - MSDS - Galvanized Steel Products](#)  
[Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VI04146E0519\)](#)

### Related Products

[C1100563](#)  
[C1100564](#)  
[C1100565](#)  
[C3030201](#)  
[C1100566](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CN-C1500403-SPEC-EN | REV 7/2023