



# Standard Underpinning T-pipe High Strength

By CHANCE Foundation Solutions  
Catalog # [C1500488](#)

Standard Underpinning Bracket T-Pipe (Std) fits SS175.



## Features

- Finish: Galvanized
- Building Code Approved: Yes

## Application

Helical Anchoring

## General

Coating	Galvanized
Finish Type	Galvanized
Shaft Type	SS
Strength Rating - Ultimate	30000 lb
Type	Underpinning
UPC	096359367871

## Dimensions

Weight	16.00 lb
--------	----------

## Certifications and Compliance

ICC-ES Evaluated	ESR 2794
LARR Certified?	RR 25984

## Logistics

Pallet Quantity	50
-----------------	----

## Product Assets

- [Engineering Drawing - Standard Underpinning Bracket - 80 KIP](#)
- [Literature - CHANCE® Building Code Evaluated Products December 2022](#)
- [Sales Drawings - Standard Underpinning Bracket - 80 KIP](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Test Documents - ICC Evaluation \(NER2794\)](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)
- [Video - Hubbell Power Systems Helical Pile Shake Table Testing \(VIO4112E\)](#)
- [Video - CHANCE® Square Shaft Installation \(VIO4148E0819\)](#)

## Related Products

[C1500299](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C1500488-SPEC-EN | REV 1/2024