



1.25" Square Shaft Lead (SS125), 8/10 x 5ft

By CHANCE Foundation Solutions
Catalog # [C1500548](#)

SS125, 60" long with 8",10" helices.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

| | |
|----------------------------|---------------|
| Capacity - Plate Grade | 50 |
| Coating | Galvanized |
| Finish Type | Galvanized |
| Helix Leading Edge Type | Sharp |
| Holding Capacity Soil (Kt) | 10 |
| Number of Helices | 2 |
| Shaft Type | SS |
| Torque Rating | 4000 ft-lbs |
| Type | Lead Sections |
| UPC | 096359513148 |

Dimensions

| | |
|--------------------------|--------------------------------|
| Anchor Helix Diameter(s) | 8 in - 10 in |
| Dimensions | 60.00 in x 10.00 in x 10.00 in |
| Height | 10.00 in |
| Length | 60.00 in |
| Length - Effective | 60.00 in |
| Weight | 44.30 lb |
| Width | 10.00 in |

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Engineering Drawing - SS125 Screw Anchors Lead Sections 1-1/4 inch SS](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Sales Drawings - SS1250 Screw Anchors Lead Sections 1-1/4 inch SS](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(V104146E0519\)](#)

Related Products

[C1500555](#)
[C3031502](#)
[C1500554](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C1500548-SPEC-EN | REV 1/2024