



1.25" Square Shaft Extension(SS125), 5ft

By CHANCE Foundation Solutions
Catalog # [C1500554](#)

SS125, 60" long no helix.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	10
Shaft Type	SS
Torque Rating	4000 ft-lbs
Type	Anchor Extensions
UPC	096359444732

Dimensions

Length	60.50 in
Length - Effective	57.75 in
Weight	28.70 lb

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Catalogs - CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)
[Engineering Drawing - SS125 Screw Anchors Extensions 1-1/4 inch SS](#)
[ISO Certificates - Centralia_Operations_ISO_9001_2015](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Sales Drawings - SS1250 Screw Anchors Extensions 1-1/4 inch SS](#)
[SDS - MSDS - Galvanized Steel Products](#)

Related Products

[PSP1500537P](#)
[C3031502](#)
[055832P](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CN-C1500554-SPEC-EN | REV 7/2023