



## 1.25" Square Shaft Extension (SS125), 10ft

By CHANCE Foundation Solutions  
Catalog # [C1500556](#)

SS125, 120" long no helix.



### Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

### Application

Helical Anchoring

### General

Coating	Galvanized
Finish Type	Galvanized
Holding Capacity Soil (Kt)	10
Shaft Type	SS
Torque Rating	4000 ft-lbs
Type	Anchor Extensions

### Dimensions

Length	120.00 in
Length - Effective	117.25 in
Weight	54.00 lb

### Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)  
[Engineering Drawing - SS125 Screw Anchors Extensions 1-1/4 inch SS](#)  
[Literature - New Construction Helical Pile Foundation System \(SF04215E\\_0419\)](#)  
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)  
[Sales Drawings - SS1250 Screw Anchors Extensions 1-1/4 inch SS](#)  
[SDS - MSDS - Galvanized Steel Products](#)

### Related Products

[PSP1500537P](#)  
[O55832P](#)  
[C3031502](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C1500556-SPEC-EN | REV 1/2024