



## 3.5" Round Shaft Extension(RS3500.300), 7ft

By CHANCE Foundation Solutions  
Catalog # [C1501241](#)

RS3500.300, 84" long with no helix.



### Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

### Application

Helical Anchoring

### General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	7
Shaft Type	RS
Torque Rating	13000 ft-lbs
Type	Anchor Extensions

### Dimensions

Length	84.00 in
Length - Effective	78.00 in
Weight	77.00 lb

### Certifications and Compliance

ICC-ES Evaluated	ESR 2794
------------------	----------

### Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - CHANCE Helical Solutions Product Catalog (CA04140E)
- ISO Certificates - Centralia\_Operations\_ISO\_9001\_2015
- Literature - New Construction Helical Pile Foundation System (SF04215E\_0419)
- Literature - CHANCE® Building Code Evaluated Products December 2022
- SDS - MSDS - Galvanized Steel Products
- Test Documents - ICC Evaluation (NER2794)
- Video - CHANCE 4.3 Helicap 3.0 Torque Graph (VIO4167E0420)
- Video - CHANCE 4.2 Helicap 3.0 Capacity Graph Tab (VIO4165E0420)
- Video - Hubbell Power Systems Helical Pile Shake Table Testing (VIO4112E)

### Related Products

- P1100814P
- 450315P
- 058331P - Single-Coil Spring Lockwasher for 3/4-in bolt



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CN-C1501241-SPEC-EN | REV 7/2023