



3.5" Round Shaft Extension (RS3500.300), 3-1/2ft

By CHANCE Foundation Solutions
Catalog # [C1501291](#)

RS3500.300, 42" long with no helix.



Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Holding Capacity Soil (Kt)	7
Shaft Type	RS
Torque Rating	13000 ft-lbs
Type	Anchor Extensions

Dimensions

Length	42.00 in
Length - Effective	35.50 in
Weight	39.40 lb

Certifications and Compliance

ICC-ES Evaluated ESR 2794

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE® Building Code Evaluated Products December 2022](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Test Documents - ICC Evaluation \(NER2794\)](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)
- [Video - Hubbell Power Systems Helical Pile Shake Table Testing \(VIO4112E\)](#)
- [Video - CHANCE® Square Shaft Installation \(VIO4148E0819\)](#)

Related Products

- [P1100814P](#)
- [450315P](#)
- [058331P - Single-Coil Spring Lockwasher for 3/4-in bolt](#)



A proud member of the Hubbell Family.