



1.5" Square Shaft Lead (SS150), ROCK-IT, 10/12 x 5ft

By CHANCE Foundation Solutions
Catalog # [C1501833](#)

SS150, ROCK-IT, 72" long with 10",12" helices.



*Representative Image

Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Carbide tip is added to the lead section to help with installation

Application

Helical Anchoring

General

Capacity - Plate Grade	80
Coating	Galvanized
Finish Type	Galvanized
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	10
Number of Helices	2
Shaft Type	SS
Torque Rating	7000 ft-lbs
Type	Lead Sections
UPC	096359766216

Dimensions

Anchor Helix Diameter(s)	10 in - 12 in
Length	60.00 in
Length - Effective	59.45 in
Weight	69.67 lb

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Installation Manuals - Installation Instructions - CHANCE® Helical ROCK-IT™ Pile](#)
[Literature - ROCK-IT Helical Pile Lead Section \(SF04112E\)](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Rock It Application Brochure \(BR04315E\)](#)
[Sales Drawings - Rock-IT \(SA1101290\)](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Test Documents - ROCK-IT Test Report \(R160401\)](#)
[Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)

Related Products

[C1500146](#)
[C1500144](#)
[C1500175](#)
[C1500896](#)
[639001](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C1501833-SPEC-EN | REV 1/2024