



## 2.875" Round Shaft Extension(RS2875.203), 5ft

By CHANCE Foundation Solutions  
Catalog # [C2784500CU](#)

RS2875.203, 60" long Extension



### Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

### Application

Helical Anchoring

### General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	9
Shaft Type	RS
Torque Rating	7000 ft-lbs
Type	Anchor Extensions
UPC	096359705369

### Dimensions

Length	63.00 in
Length - Effective	57.00 in
Weight	32.10 lb

### Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - CHANCE Helical Solutions Product Catalog (CA04140E)
- Engineering Drawing - SA2784300CU\_B
- Installation Manuals - IS-200FTI\_Rev\_A\_Oct\_2016
- ISO Certificates - Centralia\_Operations\_ISO\_9001\_2015
- Literature - New Construction Helical Pile Foundation System (SF04215E\_0419)
- Sales Drawings - SA2784300CU\_BU
- SDS - MSDS - Galvanized Steel Products
- Video - CHANCE 4.3 Helicap 3.0 Torque Graph (VIO4167E0420)
- Video - CHANCE 4.2 Helicap 3.0 Capacity Graph Tab (VIO4165E0420)
- Video - Hubbell Power Systems Helical Pile Shake Table Testing (VIO4112E)

### Related Products

- [C2784700CU - 2.875" Round Shaft Extension\(RS2875.203\), 7ft](#)
- [P0011971P](#)
- [C1500896](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CN-C2784500CU-SPEC-EN | REV 7/2023