



## Standard Underpinning T-pipe High Strength

By CHANCE Foundation Solutions  
Catalog # [C2788012](#)

Standard Underpinning Bracket T-Pipe (Std) fits 2875.276  
Wall.



### Features

- Finish: Galvanized
- Building Code Approved: Yes

### Application

Helical Anchoring

### General

Coating	Galvanized
Finish Type	Galvanized
Shaft Type	RS
Strength Rating - Ultimate	30000 lb
Type	Underpinning
UPC	096359513537

### Dimensions

Weight	12.00 lb
--------	----------

### Logistics

Pallet Quantity	50
-----------------	----

### Product Assets

- [Engineering Drawing - RS2875.276 T-Pipe for C1500121 Bracket](#)
- [Engineering Drawing - SA1500121\\_P](#)
- [Literature - CHANCE® Building Code Evaluated Products December 2022](#)
- [Sales Drawings - SA1500121\\_P](#)
- [Sales Drawings - RS2875.276 T-Pipe for C1500121 Bracket](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Test Documents - ICC Evaluation \(NER2794\)](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)
- [Video - Hubbell Power Systems Helical Pile Shake Table Testing \(VIO4112E\)](#)
- [Video - CHANCE® Square Shaft Installation \(VIO4148E0819\)](#)

### Related Products

[C1500121](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C2788012-SPEC-EN | REV 1/2024