



## 2.875" Round Shaft Extension (RS2875.276), 5ft ICC-ES (AC358)

By CHANCE Foundation Solutions  
Catalog # [C2788218](#)

RS2875.276, 60" long Extension ICC-ES (AC358)



### Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

### Application

Helical Anchoring

### General

Coating	Galvanized
Finish Type	Galvanized
Holding Capacity Soil (Kt)	9
Shaft Type	RS
Torque Rating	8900 ft-lbs
Type	Anchor Extensions
UPC	096359765127

### Dimensions

Length	60.00 in
Length - Effective	57 in
Pipe Wall Thickness	0.276
Weight	39.9 lb

### Certifications and Compliance

ICC-ES Evaluated                      ESR 2794

### Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Literature - CHANCE® Building Code Evaluated Products December 2022](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E\\_0419\)](#)
- [Sales Drawings - RS2875.276 PIPE PILES ICC-ES \(AC-358\) \(SA2788218\\_A\)](#)
- [Sales Drawings - RS2875.276 COMBO PILES ICC-ES \(AC-358\) \(SA2788219\)](#)
- [Sales Drawings - HELICAL PIER SS175 TO RS2875.276 BLD CD \(SA2788225\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)
- [Video - Hubbell Power Systems Helical Pile Shake Table Testing \(VIO4112E\)](#)
- [Video - CHANCE® Square Shaft Installation \(VIO4148E0819\)](#)

### Related Products

- [P0011971P](#)
- [450315P](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CN-C2788218-SPEC-EN | REV 1/2024