



2.875" Round Shaft Extension (RS2875.276), 5ft High Capacity Pile

By CHANCE Foundation Solutions
Catalog # [C2788381](#)



RS2875.276, 60" long Extension High Capacity Pile

Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

Application

Helical Anchoring

General

| | |
|----------------------------|-------------------|
| Coating | Galvanized |
| Finish Type | Galvanized |
| Holding Capacity Soil (Kt) | 9 |
| Shaft Type | RS |
| Torque Rating | 10500 ft-lbs |
| Type | Anchor Extensions |
| UPC | 096359766407 |

Dimensions

| | |
|---------------------|----------|
| Length | 60.00 in |
| Length - Effective | 57 in |
| Pipe Wall Thickness | 0.276 |
| Weight | 39.9 lb |

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Round Shaft Helical Piles \(BR04314E\)](#)
[Sales Drawings - Leads And Extensions Rs2875.276 High Capacity Pile](#)
[SDS - MSDS - Galvanized Steel Products](#)

Related Products

[C2788382 - 2.875" Round Shaft Extension \(RS2875.276\), 7ft High Capacity Pile](#)
P0011971P
[C2788381 - 2.875" Round Shaft Extension \(RS2875.276\), 5ft High Capacity Pile](#)
450315P



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C2788381-SPEC-EN | REV 1/2024