



2.875" Round Shaft Extension(RS2875.276), 5ft

By CHANCE Foundation Solutions
Catalog # [C2788500CU](#)

RS2875.276, 60" long Extension



*Representative Image

Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

Application

Helical Anchoring

General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	9
Shaft Type	RS
Torque Rating	8000 ft-lbs
Type	Anchor Extensions
UPC	096359712060

Dimensions

Length	63.00 in
Length - Effective	57.00 in
Weight	41.70 lb

Product Assets

- Brochures - [CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- Catalogs - [CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)
- Engineering Drawing - [SA2788300CU_B](#)
- Installation Manuals - [IS-200FTI_Rev_A_Oct_2016](#)
- ISO Certificates - [Centralia_Operations_ISO_9001_2015](#)
- Literature - [New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- Sales Drawings - [SA2788300CU_B](#)
- SDS - MSDS - [Galvanized Steel Products](#)
- Video - [CHANCE 4.3 Helicap 3.0 Torque Graph \(VI04167E0420\)](#)
- Video - [CHANCE 4.2 Helicap 3.0 Capacity Graph Tab \(VI04165E0420\)](#)
- Video - [Hubbell Power Systems Helical Pile Shake Table Testing \(VI04112E\)](#)

Related Products

- [C1500896](#)
- [P0011971P](#)
- [450315P](#)
- [C2788500CU - 2.875" Round Shaft Extension\(RS2875.276\), 5ft](#)
- [C2788700CU - 2.875" Round Shaft Extension\(RS2875.276\), 7ft](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CN-C2788500CU-SPEC-EN | REV 7/2023