



Anchor, Tool, SS225 Drive Wrench

By CHANCE Foundation Solutions
Catalog # [C3030202](#)

SS225 Drive Tool for use with 7 5/8" (193.7mm) bolt circle
Kelly Bar Adapter.



*Representative Image

Features

- These tools include our proprietary Alignment Window that helps reduce chance of finger pinch when anchor is inserted into tool.
- These drive tools require the appropriate Kelly bar adapter, sold separately
- Each comes with bolts, nuts and lockwashers.
- Includes Bent Arm Pin and Coil Lock

Application

Anchor/Pile Installation

General

Attachment Style	Kelly Bar Adapter
Bolt Grade	2
Coating	Painted
Drive Wrench Anchor Type	SS225 Anchor
EU RoHS Indicator	No
Number of Bolt Holes	12
Torque Rating	21000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359015017

Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Weight	29.400 lb

Logistics

Pallet Quantity	20
Standard Package	1

Product Assets

[Installation Manuals - CHANCE Digital Torque Indicator](#)
[Installation Manuals - Instructions for CHANCE Bolted Helical Pile Drive Tools](#)
[Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
[Literature - SF04364E Digital Torque Indicator](#)
[Sales Drawings - Anchor Wrench \(SA3031502\)](#)
[Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
[Video - Square Shaft Anchor Drive Wrench](#)
[Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

[C1100646](#)
[C1100647](#)
[PSZ0012552P - Anchor Tool Nut](#)
[PSZ0012557P - Anchor Tool Bolt](#)
[PSZ0012553P - Anchor Tool Lockwasher](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C3030202-SPEC-EN | REV 1/2024